

CAT. N° 1 380 23



DEVICE FOR EMERGENCY EXIT - 1 NO/NC - 5 A - 24 V= - RAL 6016

Pack (number of units)	1
Volume (dm ³)	0,716
Weight (g)	143,00

Product characteristics

Manual call points (MCP)

- IP 30 - IK 07
- Surface-mounting or flush-mounting (IP 30)
- Dimensions: 90x90x57 mm (surface-mounting with its base) or 90x90x24 mm (flush-mounting with flush boxes for wiring devices - drilling diameter 67 mm - for 60 mm fixing centres)
- Can be fitted on trunking Cat. Nos 0 104 63/64, 35x105 mm or 50x105 mm, with the universal support Cat. No 0 109 13
- Call by pressing the membrane (pressure 2.5 kg) with clear display of the call position
- Reset on front of device, with special key Cat. No 0 380 38 (supplied with the product)
- Possibility to add an optional mechanical status indicator Cat. No 1 380 93 to provide additional signalling
- Can receive a sealable cover Cat. No 0 380 97

Devices for emergency exit (DCMIS)

- Allow the immediate release of an exit door normally closed by an electromagnetic lock
- Color of the mechanical enclosure: green RAL 6016
- DCMIS - 1 contact
- Equipped with 1 NO/NC contact – 5 A – 24 VDC

General characteristics

Safety boxes 90 series - for fire detection and fire alarm system, emergency exit, extinguishing system, remote switching

Documentation



Catalogue pages & additional information

- [Description page \(p.695\)](#)
- [Safety boxes 90 series old range / new range chart](#)



Installation instructions & related documents

- [LE07337AC](#)