

Features

- 4mm Banana Plug.
- Rated current: 2.5A
- Rated voltage: 50V
- Max Resistance: Less than 5mΩ
- High quality and durable design.
- Line is a standard 25cm.
- Colour: Blue

RS PRO TEST LEADS

RS Stock No.: 0347237



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

- Using PVC coaxial cable line, the standard diameter for the 2.8mm.
- Flexible test lead sets are a perfect interface for multimeters configured with 4 mm sheathed safety jacks.
- Plug and housing are molded directly to the cable in an integral one piece design and the wire is double crimped for along lasting connection.
- Multi-leaf banana spring beryllium copper, nickel plated for extended insertion cycle life and low contact resistance.

General Specifications

Lead Length	L=25cm
Rated Voltage	50V
Rated Current	2.5A
Cable Material	PVC/Copper 50*0.1mm
Shield Sleeve Material	PVC
Banana body	Brass
Banana spring	Beryllium copper/Ni coated

Approvals

Certifications	CE
Declarations	RoHS, Reach, UKCA

