

213.53.100 160 bar 2nd scale psi G1/2B lower back mount

Bourdon tube pressure gauges, liquid filling,

Item number:

Quantity: 1 pcs.

Order code: 213.53-E-BG516P-GD-3KNZ-ZZZZ 53 21ACZE Z2-
ICRS004Z1ZZZ
LABEL-S61DE-##ZZZ

Overview: 213.53.100 160 bar 2nd scale psi G1/2B lower back mount
class 1.0

Triangular bezel, stainless steel, polished, with clamp

Case filling fluid: glycerine

Restrictor: brass, D 0.6

Pressure Gauge Standard: International (standard Europe)

2nd scale red

LOGO: *RS* red Pantone 185 Serial number *...*

Label: WIKA UK customer: RS (Label yellow) "Made in Poland"

414-6431

100mm G1/2B 160bar/psi

Details: Bourdon tube pressure gauges, liquid filling,
stainless steel case, model 213.53.100

Model: 213.53-E

Specifications according to data sheet: PM 02.12

Measuring system: copper alloy

Case: stainless steel 1.4301

Case: Crimp ring case (version 53)

Nominal size: 100 mm

Scale range: 0...160 bar

2nd Scale or Special Scale: 2nd scale psi

Process connection: G 1/2 B

Connector location: lower back mount

Mounting flange/bracket: Triangular bezel, stainless steel, polished, with clamp

Restrictor: brass, D 0.6

Accuracy class: class 1.0

Overpressure safe: standard

Case filling fluid: glycerine

Pointer: standard pointer

Window: polycarbonate

Packaging: single packing

Pressure Gauge Standard: International (standard Europe)

color for 2.scale (inside): red RAL 3020

customer logo beginning with: RS

LOGO: *RS* red Pantone 185

serial number on dial: Serial number *...*

Date: 25/01/2024



description field 1 (ET1): 414-6431

description field 2 (ET2): 100mm G1/2B 160bar/psi