

Datasheet

RS Pro Distribution Block, 16 mm², 25 mm², 50 mm², 12 Way, 160A, 500 V, Clear

RS Stock No: **441-4330**



Product Details

RS Pro 2-way earth block in green/yellow colour, has a nylon housing construction for longer life. This earth block has high current fingerproof screwdown terminals for easy termination. The earth block supports 6 to 16 AWG cables of 6 to 35 mm² CSA. It is current rated for 57 A and voltage rated for 800 V. It measures 54 x 10 x 62.5 mm.

Features and Benefits

- Fingerproof terminals (to VBG4 requirements)
- Flammability rating UL94V-0
- Cable sizes from 6 - 35 mm²
- Mounting method DIN rail (top hat rail)/G-rail

**Specifications:**

Cable CSA	16 mm ² , 25 mm ² , 50 mm ²
Colour	Clear
Current Rating	160 A
Height	48 mm
Housing Material	PC
Length	150 mm
Number of Ways	12
Termination Method	Screw Down
Voltage Rating	500 V
Width	84 mm
Standards Met	EN 60947-7-1:2009; UL 94V-0