



### Overview

Lead time	Usually in Stock
-----------	------------------

### General

Provided equipment	User manual
--------------------	-------------

### Physical

Cable length	1.83 m
Depth	36.5 cm
Height	12 cm
Net weight	4.5 kg
Width	13 cm

### Input

Network frequency	47...63 Hz
Plug standard	CEI 23-16 Italian
Inputvolt_other	220 V
Maximum input current	6 A
Switching current capacity	10 A
Input voltage	230 V

### Output

Rated power in W	520 W
Maximum configurable power in W	520 W
Output frequency	47...63 Hz sync to mains 50/60 Hz +/- 1 Hz unsynchronised
Outputvolt_other	220 V
UPS type	Standby
Wave type	Stepped approximation to a sinewave
Nb of power socket outlets	6 Schuko CEE 7 2 Schuko CEE 7 surge
Output voltage	230 V

## Conformance

Product certifications	CE EAC
Equipment protection policy	Lifetime : 100000 euros

## Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...90 %
Operating altitude	0...3000 ft
Ambient air temperature for storage	-15...45 °C
Storage altitude	0.00...4572.00 m
Acoustic level	45 dBA

## Batteries & Runtime

Battery type	Lead-acid battery
Number of battery filled slots	0
Number of battery free slots	0
Battery recharge time	16 h
Liquid value	0

## Communications & Management

Control panel	LED status display with on line : on battery : replace battery and overload indicators
Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm

## Surge Protection and Filtering

Surge energy rate	310 J
Data line protection	RJ45 analog phone line for phone/fax/modem/DSL RJ45 network line - 10/100 base-T Ethernet

## Packing Units

Package 1 Weight	5 kg
Package 1 Height	19 cm
Package 1 width	18.6 cm
Package 1 Length	44.1 cm
SCC14	10731304347290
Package 2 Weight	16.00 kg
Package 2 Height	203.20 mm
Package 2 width	457.20 mm
Package 2 Length	558.80 mm

## Contractual warranty

Warranty	2 years repair or replace, 3 years repair or replace for European Union countries
----------	---