

2.5

Set of internal and external extractors

Code	ETIM
2017040	EC011834
EAN	UNSPSC
4036976123746	27-11-17-12
Country of origin	eCl@ss
Germany	21-04-15-01
Customs tariff number	
82055980	



Article description

- Suitable for various applications of external or internal extraction
- Internal extractor for drill holes with \varnothing 5 - 55 mm. To be used with slide hammer or counter support
- External pullers with various spans up to 130 mm for the most diverse pulling problems
- Pulling and separating devices including extensions, ideal for pulling off tightly fitted or thin-walled parts for outside diameters 5 - 115 mm
- Everything at hand on perforated wall-board

Article parts list

1 internal extractor 5-8 mm, No. 1.30/0,1 internal extractor 8-12 mm, No. 1.30/1,1 internal extractor 12-15 mm, No. 1.30/2,1 internal extractor 15-19 mm, No. 1.30/3,1 internal extractor 19-25 mm, No. 1.30/4,1 internal extractor 25-30 mm, No. 1.30/4A,1 internal extractor 30-35 mm, No. 1.30/5,1 internal extractor 35-45 mm, No. 1.30/6,1 internal extractor 45-55 mm, No. 1.30/7,1 sliding hammer 230 mm, 700 g, No. 1.35/1A,1 sliding hammer 500 mm, 1,7 kg, No. 1.35/2,1 counter-support brace for 1.30/0 - 1.30/5, No. 1.36/1,1 counter-support brace for 1.30/6 - 1.30/7, No. 1.36/2,1 universal puller HIGH POWER 2-arm pattern 130x100 mm, No. 1.04/HP1A,1 battery-terminal puller, 3-arm pattern 70x80 mm, No. 1.13/00,1 puller with extra slim legs 80x85 mm, No. 1.23/15,1 separator puller 40-120 mm, No. 1.38/0,1 separator puller 70-215 mm, No. 1.38/2,1 extension rod M10, No. 1.38/AV,1 extension rod M14x1.5, No. 1.38/CV,1 bearing separator 5-60 mm, No. 1.40/0,1 bearing separator 22-115 mm, No. 1.40/2

Article information

Contents (Qty of pieces)	22	Quick release lever available	no
Version/Execution	inclusive perforated wall panel	3D data available	no
Graduation	no	Spindle anti-slip device	no
reversible arms available	no	Screws included	no
Clamping bracket available	no	Anti-slip device on the spindle	no
Net weight [kg]	29 kg	Exchangeable spindle tip	no
Hook brake available	no	Can be retrofitted with hydraulic spindle	no
Hook can be moved parallel	no		