



DCG430N-XJ

18 Volt Cordless Compact Multi-Material Cutter

- Innovative compact series – maximum power in an exceptionally compact, ergonomic and functional design
- Paddle switch – for enhanced user safety
- Perform & Protect: Electronic brake and clutch – stops the tool quickly and helps protect the user and tool in the event of a stall
- Forward and reverse – allows quick direction changes for greater flexibility in use
- Rubber overmoulded grip and ergonomic, compact design with an optimised centre of gravity – for comfortable and secure handling
- Mesh guard – helps protect the motor and electronics from dust and debris
- Single Allen bolt clamping – requires only one Allen key and the spindle lock for quick and easy accessory changes
- Tool-free adjustable guard – for safe and convenient working
- Spindle lock – enables quick and easy wheel changes
- Optimised for POWERSTACK™ batteries – delivering maximum performance, compact size and long runtime; compatible with all DEWALT 18V XR batteries and DEWALT XR FLEXVOLT batteries

Standard scope of delivery

- Guard
- Assembly tool
- 1x 76 mm multi-material diamond cutting blade
- 1x 76 mm cutting wheel for metal and stainless steel

Technical data

Battery technology	18 volt XR or XR Flexvolt batteries
No-load speed (min ⁻¹)	20.000
Disc diameter (mm)	76
Disc thickness (maximum in mm)	3
Drive spindle	M10
Weight (without battery; kg)	1,1
Triaxial Vibration (m/s ²)	3,8
Uncertainty factor K1 (m/s ²)	1,5
Sound pressure level LPA (dB(A))	85
Sound power level LWA (dB(A))	93
Uncertainty factor (dB(A))	3
EAN-code	5035048834572