

ME MAX B-22,5 BU - Filler plug



2697136

<https://www.phoenixcontact.com/gb/products/2697136>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail housing, Filler plug for unoccupied terminal points, width: 20 mm, height: 21.6 mm, depth: 8.1 mm, color: blue (similar RAL 5015)

Your advantages

- Easy, tool-free mounting
- Plastic in accordance with UL94 V0: for more rigorous flammability requirements

Commercial data

Item number	2697136
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	ACHABZ
Product key	ACHABZ
GTIN	4017918978778
Weight per piece (including packing)	1.32 g
Weight per piece (excluding packing)	1.316 g
Customs tariff number	39269097
Country of origin	DE

ME MAX B-22,5 BU - Filler plug



2697136

<https://www.phoenixcontact.com/gb/products/2697136>

Technical data

Notes

Assembly note	Please observe the application note in the download area.
---------------	---

Product properties

Product type	Filler plug
Housing type	DIN rail housing
Housing series	ME-MAX
Product family	ME MAX 22,5..
Type	Filler plug for unoccupied terminal points
Ventilation openings present	no

Dimensions

Width	20 mm
Height	21.6 mm
Depth	8.1 mm

Material specifications

Color (Housing)	blue (RAL 5015)
Flammability rating according to UL 94	V0
CTI according to IEC 60112	600
Housing material	PA
Surface characteristics	untreated

Environmental and real-life conditions

Ambient conditions

Max. IP code to attain	IP20
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	80 %

Mounting

Mounting type	Latching
---------------	----------

Packaging specifications

Outer packaging type	Resealable bag
----------------------	----------------

ME MAX B-22,5 BU - Filler plug

2697136

<https://www.phoenixcontact.com/gb/products/2697136>



Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/2697136>



UL Recognized

Approval ID: E240868

ME MAX B-22,5 BU - Filler plug



2697136

<https://www.phoenixcontact.com/gb/products/2697136>

Classifications

ECLASS

ECLASS-13.0	27190605
-------------	----------

ETIM

ETIM 9.0	EC002779
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

ME MAX B-22,5 BU - Filler plug



2697136

<https://www.phoenixcontact.com/gb/products/2697136>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk