

**ENGLISH** 

# RS PRO Fahrenheit/Centigrade Dial Dry Temperature Gauge Suitable For Various Applications

**Brand: RS PRO** 

RS Stock No.: 324-8407



#### Model Selection (RS stock number 324-xxxx)

Bottom	Scale	Garla dia 100mm		00mm
connection		L = 50mm	L = 100mm	
-20 to +60 °C	Celsius & Fahrenheit	324-8384	324-8407	
0 to +120 °C	Celsius & Fahrenheit	324-8413	324-8429	

Back	Scale	dia 100mm	
connection		L = 50mm	L = 100mm
-20 to +60 °C	Celsius & Fahrenheit	324-8435	324-8873
0 to +120 °C	Celsius & Fahrenheit	324-8441	324-8463

#### **Product Details**

Centre Back and Vertical 100mm Diameter Immersion Thermometers

Bi-metal element thermometers with applications in the heating and ventilation process, and refrigeration industries

**Dual scale** 

**Acrylic Window** 

Temperature range covers both hot & chilled water applications

Manufactured to DIN 16203

1/2 in. BSP Brass Male Thread

Vertical entry types: 324-8384, 324-8413, 324-8407, 324-8429

Standards DIN 16203

### **Specifications**

Min. Temperature Sensed

Temperature Sensitive Range -20 → +60°C

Attribute	Value
Thermometer Type	Dial
Suitable Applications	Heating & Ventilation, Refrigeration Industry
Temperature Scale	Both
Filling Type	Dry
Case Material	Steel
Case Diameter	100mm
Max. Temperature Sensed	+60°C

-20°C

## **Drawing**



