








Color: ■ dark gray/yellow





Physical data	
Width	43 mm / 1.693 inches
Height	23.7 mm / 0.933 inches
Depth from upper-edge of DIN-rail	33.2 mm / 1.307 inches
Depth	39.5 mm / 1.555 inches

Mechanical data	
Mounting type	Snapping on
Mounting type	DIN-35 rail
Suitable	for 10-wire connectors (4 mm²)

Material data	
Note (material data)	Information on material specifications can be found here
Color	dark gray/yellow
Material group	I
Insulation material (main housing)	Polyamide (PA66)
Flammability class per UL94	V0
Fire load	0.182 MJ
Weight	6.1 g

Commercial data	
PU (SPU)	10 pcs
Packaging type	Box
Country of origin	CN
GTIN	4066966603781
Customs tariff number	39269097900

Product Classification	
UNSPSC	39121421
ETIM 9.0	EC002848
ECCN	NO US CLASSIFICATION

Environmental Product Compliance	
RoHS Compliance Status	Compliant,No Exemption

Downloads	
Environmental Product Compliance	
Compliance Search	
Environmental Product Compliance 221-549/002-053	



1 Compatible Products
1.1 Optional Accessories
1.1.1 Marking
1.1.1.1 Marking strip



Item No.: 210-833
Marking strips; 25 m on roll; 6 mm wide;
plain; Self-adhesive; white