ZB4BS8447

red Ø40 Emergency stop, switching off head Ø22 trigger and latching turn release





Main

Range of product	Harmony XB4	
Product or component type	Head for emergency switching off push-button	
Device short name	ZB4	
Bezel material	Black metal	
Mounting diameter	22 Mm	
Sale per indivisible quantity	1	
Shape of signaling unit head	Round	
Type of operator	Trigger action and mechanical latching	
Reset	Turn to release	
Operator profile	Red mushroom Ø 40 mm, unmarked	
Head type	Standard	

Complementary

Device presentation	Basic element
	C15 for <1 contacts using single blocks in front mounting C10 for <4 contacts using single and double blocks in front mounting
	C11 for <3 contacts using single blocks in front mounting
	C8 for <4 contacts using single and double blocks in front mounting
Electrical composition code	C7 for <4 contacts using single blocks in front mounting
Mechanical durability	300000 Cycles
Resistance to high pressure washer	7000000 Pa at 55 °C, distance : 0.1 m
Net weight	0.073 Kg
CAD overall depth	57 Mm
CAD overall height	40 Mm
CAD overall width	40 Mm

Environment

Protective treatment	TH
Ambient air temperature for storage	-4070 °C
Ambient air temperature for operation	-4070 °C
Electrical shock protection class	Class I conforming to IEC 61140
IP degree of protection	IP66 conforming to IEC 60529 IP69 IP69K
NEMA degree of protection	NEMA 13 NEMA 4X NEMA 4 NEMA 12

IK degree of protection	IK06 conforming to IEC 50102
Standards	EN/IEC 60204-1
	JIS C8201-5-1
	IEC 60364-5-53
	CSA C22.2 No 14
	EN/IEC 60947-5-1
	GB 14048.5
	EN/IEC 60947-1
	UL 508
	EN/ISO 13850
	EN/IEC 60947-5-4
	EN/IEC 60947-5-5
	JIS C8201-1
Product certifications	CSA
	BV
	RINA
	DNV
	LROS (Lloyds register of shipping)
	UL listed
	GL
Vibration resistance	5 gn (f= 2500 Hz) conforming to IEC 60068-2-6
Shock resistance	30 gn (duration = 18 ms) for half sine wave acceleration conforming-
	to IEC 60068-2-27
	50 gn (duration = 11 ms) for half sine wave acceleration conforming-
	to IEC 60068-2-27
Packing Units	
Package 1 Weight	76 G
achage i weight	100

Package 1 Weight	76 G
Package 2 Weight	6.529 Kg

Offer Sustainability

Office Oddital lability	
Sustainable offer status	Green Premium product
REACh Regulation	☑REACh Declaration
REACh free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EVEU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	€Yes
China RoHS Regulation	☑ China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	18 months

Product Life Status : Commercialised

