

Datasheet

## RS Pro #2410WC Digital Thermometer, 3 Input LCD

RS Stock No: 408-6109



### Product Details

RS Pro digital thermometer displays time, temperature (select indoor or outdoor) and relative humidity in a large 3-channel display. This multi-purpose device operates at a temperature range of 0 to +40°C (resolution 0.5°C). It uses 1 x AAA battery for a superior performance.

### Features and Benefits

- 3 m external temperature sensor
- Selectable °C/°F
- 12/24 hours time selectable
- Min/max temperature and humidity memory recall
- Dimensions: 108 x 58 x 15 mm

**Specifications:**

Absolute Maximum Temperature Measurement	+70°C
Application	Multi-Purpose
Battery Type	AAA
Best Accuracy	±1%
Dimensions	108 x 58 x 15 mm
Height	15 mm
Length	108 mm
Minimum/Maximum Recordings	Yes
Number of Temperature Inputs	3
Resolution	0.5°C
Temperature Scale	Centigrade, Fahrenheit
Thermometer Type	LCD
Width	58 mm
Instrument Measurement Range	-50 to +70°C