

FEATURES

- **Sintered Bronze Material:** Offers excellent wear resistance and durability.
- **Flanged Design:** Provides easy installation and secure positioning.
- **Dynamic Load Rating of 14 N/mm²:** Ensures reliable performance under moving loads.
- **Static Load Rating of 50 N/mm²:** Supports high load capacity when stationary.
- **0.62 in Bore Size:** Suitable for a variety of shaft sizes.
- **0.87 in Outside Diameter:** Compatible with standard housing dimensions.
- **1-1/8 in Width:** Provides stability and support in applications.

RS PRO 0.62 in Flanged Plain Bearing

RS Stock No: 528-862



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO flanged plain bearing is designed for efficient and reliable operation in various industrial applications. Made from high-quality sintered bronze, it provides excellent durability and performance under both dynamic and static loads. Ideal for use in machinery where low maintenance and high load capacity are essential.

General Specifications

| | |
|---------------------|----------------------|
| Bore Size | 0.62 in |
| Dynamic Load Rating | 14 N/mm ² |
| Product Type | Plain Bearing |
| Static Load Rating | 50 N/mm ² |
| Sub Type | Flanged |

Mechanical Specifications

| | |
|------------------|-----------------|
| Material | Sintered Bronze |
| Outside Diameter | 0.87 in |
| Width | 1-1/8 in |

Approvals

| | |
|---------------------|-------------------------|
| Standards/Approvals | ISO 9001:2008, UKAS 001 |
|---------------------|-------------------------|

