

6225

Assembly gloves
PPE risk category II



Particularly sensitive
Perfect for working with small parts
Very good tactile sensitivity

15
GAUGE



PU

3D
FIT

6225



Material:	Nylon, grey
Coating:	PU, black
Size(s):	6-11
Packaging unit:	120 pair(s)
Certification:	EN 388, OEKO-TEX STANDARD 100®

NITRAS assembly gloves, nylon, grey, PU coating, black (colour code: 1210), partly coated on palm and fingertips, knitted wrist, perfect and innovative fit thanks 3D FIT, unique comfort and protection for the user, perfect dexterity, premium quality, OEKO-TEX STANDARD 100®



EN ISO 21420

15
GAUGE



Size	6	7	8	9	10	11
Colour coding system						

Industries

-  Craft
-  Building / Construction
-  Automotive manufacturing
-  Commissioning / shipping
-  Landscape gardening

Advantages

- + Particularly sensitive
- + Perfect for working with small parts
- + Very good tactile sensitivity



Performance values

EN 388:2016 + A1:2018	Test parameter	Performance levels	Test result
 4141X	Abrasion resistance	1-4	4
	Blade cut resistance (Coupe-Test)	1-5	1
	Tear resistance	1-4	4
	Puncture resistance	1-4	1
	Blade cut resistance (TDM)	A-F	X
EN ISO 21420:2020	Test parameter	Performance levels	Test result
	Dexterity	1-5	5

Additional information

	Material	Colour
Palm	PU on nylon	black
Index finger and thumb	PU on nylon	black
Back of the hand	Nylon	grey
Fingertips	PU on nylon	black
Cuff / knitted wrist	PU on nylon	grey

Logistics data

Size	GTIN (SPU)	GTIN (PU)	Length (m)	Width (m)	Height (m)	Weight (kg)	Quantity PU / pallet
6	4059904216709	4059904216761	0,47 m	0,39 m	0,34 m	4,8 kg	18
7	4059904216716	4059904216778	0,47 m	0,39 m	0,35 m	5,04 kg	18
8	4059904216723	4059904216785	0,48 m	0,39 m	0,35 m	5,22 kg	18
9	4059904216730	4059904216792	0,47 m	0,39 m	0,34 m	5,75 kg	18
10	4059904216747	4059904216808	0,48 m	0,4 m	0,34 m	6,31 kg	18
11	4059904216754	4059904216815	0,48 m	0,4 m	0,34 m	6,37 kg	18

Customs tariff number: 61161080910

Country of origin: China