

**ARCANOL-VIB3-400G** [↗](#)

Bearing grease

Special grease ARCANOL-VIB3

Technical information

Your current product variant

Grease category	SG	Special greases
Package size	400 G	400 g cartridge

Technical data

$\vartheta_{O \min}$	-30 °C	Operating temperature, min.
$\vartheta_{O \max}$	150 °C	Operating temperature, max.
ϑ_G	90 °C	Upper continuous limit temperature
$n \cdot d_M$	350.000 mm/min	Speed of rotation specific value
	Lithium complex soap	Thickener type
	Mineral oil	Base oil type
v_{40}	170 mm ² /s	Base oil viscosity at +40°C
v_{100}	14 mm ² /s	Base oil viscosity at +100 °C
	3	NLGI class
	Special grease	Grease category
ρ	0,9 kg/dm ³	Density
	400 g cartridge	Container
$\approx m$	435,7 g	Weight