

Impact Wrench LXT®

DTW700

18V • 1/2" • 700 Nm • 0 – 2 200 min⁻¹

3 modes of reaction time for automatic stop available both in forward and reverse rotation modes

A powerful, brushless 1/2" drive impact wrench with a fastening torque of up to 700 Nm. Three different power settings. Equipped with twin LED lights for added lighting, this tool is ideal for applications that require high fastening torque.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Max Fastening Torque Impact Drill	150 / 200 / 320 / 700 Nm
No load speed	0 - 500 / 1200 / 1900 / 2200 min ⁻¹
Impacts per Minute (IPM)	0 - 1000 / 1700 / 2400 / 2700 min ⁻¹
Drive Square	1/2 "
Tightening Capacity Standard Bolt	M10 - M24
Sound Power Level (L _{WA})	105 dB(A)
Sound Pressure Level (L _{pA})	97 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	2,3 - 2,7 kg
Product Dimensions (L x W x H):	170 x 81 x 276 mm
Brushless Motor	✓

User benefits

- Brushless maintenance-free and long-life motor
- LED light illuminates the work site
- Battery protection system automatically shuts off power when the battery level is low
- Ergonomic chassis design ensures a good working position.
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- 3 modes of reaction time for automatic stop available both in forward and reverse rotation modes

Link to product - www.makitauk.com



Related products

■ Optional AC

191G67-2

Extension handle



■ Other

User manual

Parts drawing