

ENGLISH

Datasheet

RS Pro Plain Stainless Steel Flat Head Machine Screws, M4 x 12mm

RS Stock No: 158-3382



Product Details

RS Pro machine screw measuring M4 x 12 mm, is made of type 316 S16 plain A4 grade 18/8 stainless steel, which has higher level of corrosion resistance than A2 stainless steel. The flat head screw can be used at up to 300°C. The slotted drive screw is suitable for use in food, medical, chemical, construction and electronic applications.

Features and Benefits

- A4 grade 18/8 stainless steel (Type 316 S16) construction
- Higher level of corrosion resistance than A2 S/S
- Suitable for use up to 300°C
- Suitable for use in most food, medical, chemical, construction and electronic applications



ENGLISH

Specifications:

Drive Type	Slot
Finish	Plain
Head Shape	Countersunk
Material	Stainless Steel
Length	12 mm
Stainless Steel Type	316 (A4)
Thread Pitch	0.7
Thread Size (Metric)	M4
Head Diameter	8.04 to 8.4 mm
Head Height	2.7 mm
Slot Depth	1 to 1.3 mm
Slot Width	1.2 mm
Specification	DIN 963