

Heavy Duty Cast Iron Foot Switch

RS Stock No. 116-732



Degree of protection	IP20
Materials of Construction	Cast iron
Colour	Black
Cable Connection	Adjustable strain relief connector.
Contact Action	SPDT maintained. Push -'On', Push -'Off' action.
Electrical Rating	20A-125V a.c., 10A-250V a.c., 1kW-120/240V a.c.
Features & Benefits	Rugged cast metal construction with proven reliability. Two holes provided for rigid mounting to floor or equipment.
Weight	1.0kg
Size	(See below)

