



# Ty-Rap<sup>®</sup>


## Premium cable ties with steel locking barb Standard ties



### Approvals



E49405



### Technical Information

Material	Polyamide 6.6
Temperature range	-40°C to +85°C
Colour	Black
Flammability rating	UL 94 V-2
Other properties	UV-resistant, Halogen free, Silicone free

### Ordering Information: Polyamide 6.6 UV-stabilised cable ties

PRODUCT REF.	MIL SPEC.	LENGTH	WIDTH	THICKNESS	BUNDLE DIAMETER	MINIMUM TENSILE STRENGTH	QUANTITY	TOOLING
		L [mm]	W [mm]					
TY23MX / TYB23MX	MS-3367-4	92	2.4	1.0	2 - 16	80	1000	
TYB2315MX	-	178	2.4	1.0	2 - 32	80	1000	
TY232MX	-	203	2.4	1.0	2 - 50	80	1000	
TY234MX	-	356	2.4	1.0	2 - 102	80	1000	ERG299
TY24MX / TYB24MX	MS-3367-5	140	3.6	1.1	2 - 29	130	1000	WT193A
TY242MX	-	208	3.6	1.1	2 - 50	130	1000	TR227
TY26MX	-	284	3.6	1.1	2 - 76	130	1000	
TY244MX	-	368	3.6	1.1	2 - 103	130	1000	
TY25MX / TYB25MX	MS-3367-1	186	4.8	1.1	3.5 - 45	220	1000	ERG297
TY253MX	MS-3367-7	290	4.8	1.1	3.5 - 78	220	1000	ERG299
TY28MX	MS-3367-2	360	4.8	1.1	3.5 - 102	220	1000	WT193A, TR227
TY271MX	-	150	7.6	1.5	6 - 31	540	500	
TY272MX	-	222	7.6	1.6	6 - 50	540	500	
TY27MX	MS-3367-3	340	7.0	1.6	6 - 90	540	500	L-500-EU
TY275MX	-	457	7.0	1.6	6 - 127	540	500	ERG297
TY277MX	-	617	7.0	1.6	6 - 177	540	500	
TY29MX	MS-3367-6	771	7.6	1.6	6 - 229	540	500	
TY53510MX	-	889	8.1	1.7	to 254	780	50	WT3D
TY54513MX	-	1143	8.1	1.7	to 330	780	50	L-500-EU

Description of packing sizes: see page 10

Description of materials and properties: see pages 102 to 109

For tooling specifications, see pages 92 to 99