

Han 24HPR-HBM -break-away



Image is for illustration purposes only. Please refer to product description.

Part number	09 40 024 4321
Specification	Han 24HPR-HBM -break-away
HARTING eCatalogue	https://harting.com/09400244321

Identification

Category	Hoods / Housings
Series of hoods/housings	Han [®] HPR
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	With metal cover
Features	Corrosion resistance ASTM B117-09 (500 h)

Version

Size	24 B
Locking type	Break-away
Field of application	Hoods/housings for harsh outdoor environments

Technical characteristics

Tightening torque	3 Nm Fixing screws M6
Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP69K IP65 / IP68

Material properties

Material (hood/housing)	Aluminium die-cast Corrosion resistant
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	Silicone
Material (locking)	Stainless steel



Pushing Performance
Since 1945

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	IEC 61373
	IEC 60529
	EN 45545

Commercial data

Packaging size	1
Net weight	737.8 g
Country of origin	India
European customs tariff number	85389099
GTIN	5713140444102
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466