

GH FAST RANGE

GH Series External Camera Housing



The innovative and stylish design of the new GH Fast housing makes the installation of this external camera housing much simpler and easier for the installer.

Dual access, from either side of the housing is made possible due to its unique dual side opening hinges. The hinged lid runs along the length of the housing body and permits lots of room for work during installation of camera and lens. And, since the housing can be opened from either side any additional set-up can be made easily at the installation location.

The GH Fast housing is manufactured from the latest techno-polymer which gives the housing an IP rating of IP66 and protection against harmful UV rays. This material also makes the housing vandal resistant to IK10 EN50102.

The GH Fast housing is supplied as standard with external sunshield and cable managed wall bracket. The units are also pre-cabled with a coaxial cable for video and power cord for voltage. Due to the design of the housing once installed they require little or no maintenance.

Ordering Codes:

- GH-FWC230 External housing sunshield and wall bracket 230Vac
- GH-FWC24 External housing sunshield and wall bracket 24Vac
- GH-FWC12 External housing sunshield and wall bracket 12Vdc

| Model | GH-FW230 | GH-FW24 | GH-FW12 |
|-----------------------|--|---------|---------|
| Ingress Protection | IP66 | | |
| Input Voltage | 230Vac | 24Vac | 12Vdc |
| Power Consumption | 40mA | 350mA | 700mA |
| Operating temperature | -20deg-50deg | | |
| Dimensions | 128 (w)x66(h)x220(l)mm, Sunshield 391(l)mm | | |
| Weight | Approximately 2.1Kg including cables | | |

KEY FEATURES:

- Hassle free
- Simple to Install
- IP66 Housing
- Anti Vibration camera system
- Double side opening
- Cable managed
- Adjustable sunshield
- Different mounting options