

5

4

3

2

1

DRAWING NO.  
27-9008

REVISIONS

01	OFFICIAL RELEASE				2009.09.0
	08-18-09	L	L	H	Betty 2009.33.18 +08'00'

Description: CP88T50 BNC(M) 50Term, NO Chain  
 Part No: 27-9008  
 Application: N/A  
 Crimp Tool: N/A  
 Impedance: 50 ohm  
 Frequency Range: 0~1 GHz  
 Material: Body Brass Nickel plated  
 Insulator Delrin  
 Contact Brass Gold plated  
 Nut Zinc Nickel plated  
 Lable Self adhesive PE  
 RoHS Compliance: Yes  
 Technical Detail: Refer to Emerson Document P/N 27-0000



D

C

D


C

受控 CONTROLLED DOCUMENT

编号 P/N	27-9008-C UST	版本 Rev	01	日期 Rel'd Date	SEP 14,09
-----------	---------------	-----------	----	------------------	-----------

B

B



CUSTOMER COPY

A

A

DIM OUTLINE

TOLERANCE UNLESS OTHERWISE SPECIFIED		DRAWN BY LINDA.WU	DATE 08-18-09
DECIMALS	mm	CHECKED BY LINDA.WU	DATE 08-18-09
X	± 0.5	APPROVED BY THOMAS	DATE 08-18-09
X.X	± 0.3	U/M	mm
X.XX	± 0.1		
ANGLES	± 0.5°		

**EMERSON**  
Network Power

**Connectivity Solutions**

TITLE  
CP88T50 BNC(M) 50TERM, NO CHAIN

THIS DRAWING WAS PRODUCED BY COMPUTER,  
DO NOT SCALE DRAWING OR UPDATE MANUALLY.

SHEET 1 OF 1	DRAWING NO. 27-9008	SIZE A
-----------------	------------------------	-----------

5

4

3

2

1