



ENGLISH

## Datasheet

# Yellow Crimp Ring Terminal, M8 Stud Size, 12 to 10 AWG

RS Stock number [613-9283](#)



### Description:

Yellow crimp ring, 4.0 - 6.0 mm<sup>2</sup>

### Insulated Funnel Entry

This range of funnel entry terminals guarantees total insertion of the conductor strands into the terminal barrel.

- Improved contact and tensile strength due to 'rifled' barrel
- Terminal design ensures a reliable electrical and mechanical connection
- Electrolytically tin plated body with various insulation options including polycarbonate, vinyl, PVC and nylon
- Popular items also available in kits, typically stock number [613-9952](#)

### Specifications:

Colour:	Yellow
Contact Material:	Copper
Insulation Material :	Vinyl
Overall Length:	34mm
Stud Size:	M8
Wire Size:	12 → 10 AWG
Maximum Electrical Rating:	75°C 600 Volts Max.

