



*Instruction sheet for the safe use of the
3 Wheeled Drum Dolly (3WDD) & Drum Truck (DT, DT/RW)*

1. Offer Drum up to the dolly on one of the open sides



2. With care lower the drum on to the dolly supports



3. To remove the drum reverse the above



Fig. 1

3 Wheeled Drum Dolly

Designed for 210 Ltr Steel Drums, allowing for safe loading and off loading in conjuncture with a Drum truck see Fig 1.

Specification

Size - 735mm Dia x 125mm high overall

Wheels - 75mm Dia - Nylon

Capacity - 250Kg

Weight - 8Kg Approx



Drum Truck (DT) & with rear wheels (DT/RW)

Designed for 210Ltr Drums (See Fig2)



DT



DT/RW

	DT	DT/RW
Size	1520 x 610 x 420mm (nom) H x W x D	1520 x 610 x 420mm (nom) <i>Attachment</i> 185mm high x 430 x 50mm
Wheels	250mm Dia Solid Rubber Tyres	250mm Dia Solid Rubber Tyre <i>Attachment</i> (x2) 100mm swivel castor
Capacity	270Kg	270Kg
Weight	24Kg Approx	24Kg Approx

Fig. 2



1. Ensure that the truck toes touch the outer edge of the drum and position the handle vertically above the wheels. Lift the hook over the drum rim
2. Whilst gripping the two handles & pushing with one foot on the rest, tilt the drum towards the operator.
3. The two toe plates ensure safe and comfortable positioning. The Rear wheels ensure support.