

Datasheet

RS Pro Chrome Plated Zinc Alloy Adjustable Compression Latch

RS Stock No: 136-3602



- Adjustable grip range between 14 and 73mm using one of three cams. Cranked cam 1: 14-25mm (62-73 with cam reversed). Cranked cam 2: 26-37mm (50-61mm with cam reversed). Flat cam 38-49mm.
- Chrome plated zinc die cast construction with zinc plated steel cams.
- 7mm square key operation with locked indicator on the latch head. Use RS key 341-0286.
- Rotating the key by 180° clockwise to lock closes the latch by 90° giving a pull up of 5.5mm to provide excellent gasket sealing. To unlock rotate the key by 180° anti-clockwise and at the same time push down on the key.
- IP65 sealed.
- Vibration resistance in the locked position is provided by a cross pin in the shaft that locates in a cut out in the housing.
- Maximum panel thickness of door - 20mm. There is no minimum thickness.
- Left hand, right hand, 12 o'clock, and 6 o'clock locking positions provided for.
- External size on door: 28mm diameter x 5mm deep.
- Installation cut out in door: 22.2mm dia. x 19.2mm.
- Weight: 0.175 Kg.

