

Project..... Comments.....

Fixture Type..... Prepared By.....

**Product Description:**

Registered Community Design - 001861261. IP65 high power LED fire rated downlight. Integrated LED driver connected to loop-in / loop-out FASTFIX connector (Included). Tested in 30, 60 & 90 minute fire rated ceilings. Tested to BS476 Part 21. Tested to BS EN ISO 140-3:1995 & BS EN ISO 140-6:1998 (Acoustics) confirming that they maintain the ability for an internal or separating floor to provide sound insulation. Dimmable (AU-FRLD911, AU-FRLD913) and non-dimmable (AU-FRL901, AU-FRL903) versions available (dimmable with leading/trailing edge dimmers).

**Product Image & Dimensions:**



Overall Diameter 88 mm

**Product Specifications:**

- Input Voltage (Min): 100 V
- Input Voltage (Max): 240 V
- Input Voltage Type: AC
- Dimmable: No
- Beam Angle: 40 °
- IP Rating: IP65
- Cutout Diameter: 65-72 mm
- Recess Depth: 105 mm
- Overall Diameter: 88 mm
- Guarantee: 7 Years

**Compliance & Approvals:**



**SKU Table and Ordering:**

SKU Code	Wattage	Colour Temperature	Lumens	Finish Colour	EAN	Qty
AU-FRL903W/30	9 W	3000 K	420 lm	White	5055155472238	<input type="text"/>
AU-FRL903W/40	9 W	4000 K	430 lm	White	5055155472269	<input type="text"/>

**Warranty:**

For available warranty information for this product, please visit:

<http://gb.auroralighting.com/Products/Indoor-Luminaires/Fire-Rated-Downlighting/i9/100-240V-LED-IP65-Fixed-9W-i9-Downlight-Fire-Prote.aspx>

**UK Sales**

16 Alban Park  
Hatfield Road, St. Albans  
United Kingdom  
PH: +44 (0) 1727 83 66 11  
FX: +44 (0) 1727 83 66 22

**UK Distribution**

Apex Park, 6 Little Burrows  
Burrowfields, Welwyn Garden City  
AL7 4SW  
United Kingdom  
PH: +44 (0) 1707 35 18 20  
FX: +44 (0) 1727 35 18 21