
## electrical connection box VAVE-L1-1H3-LR Part number: 566717



## **Data sheet**

Feature	Value	
Assembly position	Any	
Polarity protected	for operating voltage	
Additional functions	Spark arresting	
	Reduction of holding current	
Signal status display	LED	
Nominal operating voltage DC	24 V	
Surge strength	0.8 kV	
Degree of contamination	3	
Authorisation	RCM Mark	
CE mark (see declaration of conformity)	to EU directive for EMC	
Corrosion resistance classification CRC	0 - No corrosion stress	
Protection class	IP40	
Ambient temperature	-5 60 °C	
Product weight	1.5 g	
Electrical connection	Plug socket	
	2-pin	
Protective earth connection	Not available	
Mounting type	Clip	
Housing colour	Black	
Materials note	Conforms to RoHS	
Material housing	PA	

## **FESTO**