

Plunge Cut Saw LXT®

DSP601

18V X2 • 2 500 – 6 300 min⁻¹ • 165 mm

Precise brushless plunge cut circular saw with remote start for dust extraction for professionals

A precise plunge cut circular saw with a brushless motor. Two 18V LXT batteries give a voltage of 36V. This fast saw has an adjustable speed of between 2 500 and 6 300 min⁻¹. Extremely neat cutting with a guide rail. Remote start for dust extraction.



18V 18V → 36V LXT BL MOTOR ADT AWS

Technical specifications

Nominal Battery Voltage	2 x 18 V
Voltage LXT	✓
Max. Cutting Depth at 90°	56 mm
Max. Cutting Depth at 45°	40 mm
No load speed	2500 - 6300 min ⁻¹
Sound Power Level (L _{WA})	103 dB(A)
Sound Pressure Level (L _{pA})	95 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	4,4 - 5,1 kg
Product Dimensions (L x W x H):	346 x 241 x 272 mm
Brushless Motor	✓
Max. Cutting Depth at 48°	38 mm
AWS ready	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion

User benefits

- Brushless maintenance-free and long-life motor
- Magnesium components create lightweight saws that are well-balanced and job site tough
- The rubber coating on the handle ensures a firm working grip
- ADT (Automatic torque Drive Technology) adjusts speed and torque during operation for optimum performance
- Electric brake for maximum productivity and increased operator safety
- Auto-start Wireless System (AWS) connects to compatible vacuum cleaners with Bluetooth
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makitauk.com



Related products

Optional AC

194367-7 Guide rail, 3 000 mm		196664-7 Bevel guide set	
198885-7 Guide rail joint connector set, 2 pcs		199140-0 Guide rail, 1 000 mm	
199826-6 Quick-Release Ratcheting Guide Rail		783203-8 Hex Wrench 5 Mm	
821552-6 Makpac case (4)		839290-6 MakPac (4) Inlay	

Other

User manual

Parts drawing