

EXAWATT10 – ref 798751

Portable Power Station 1024Wh / 1800W



Product Overview

- Multi-purpose portable power station
- Can be used to power small appliances such as a cooler, microwave, lighting, and to recharge power tool batteries.

Product Benefits

- **1800W Output Power:** Allows you to power chargers, lighting, and appliances consuming up to 1800W (mitre saw, circular saw, microwave, kettle).
- **1024Wh LFP Battery:** LFP technology ensures a long lifespan (minimum 3000 charge/discharge cycles).
- Robust and very easy to use

Technical Specifications

GENERAL FEATURES

- Battery Energy: 1024Wh (25.6V-40Ah)
- Battery Type: LFP Lithium Iron Phosphate (80% of initial charge available after 3000 full charge & discharge cycles)
- 230 V inverter: 1800W pure sine
- Peak power 2200W
- Built-in 4W lighting
- EPS (Emergency Power System) Mode
- Display: LCD display showing % of battery remaining, charging and discharging power
- Operating Temperature:
- Discharge (-20/+60°C) - Charge (0/+50°C)
- Dimensions (LxWxH): 390*243*313 mm
- Weight: 14.25 kg

CHARGING MEANS

- Mains : Cable provided (1h00)
- Solar panel: Not included: up to 600W max (Voc panel: 12-80V)

OUTPUTS

- 230V AC sockets x 2: 1800W (total)
- DC 12V Cigarette Lighter Socket x 1: 120W max
- USB-A fast charging x1: 5V 18W max
- USB-C x 1 to 100W max

Compliant panels : 160W (#39209), 200W (#39210), 315W (#39211), 400W (#39212), 200W (39255), 440W (798770)

Logistics

EAN	3545417987515
Packing Height	40,5 cm
Packing Length	48,3 cm
Packing Width	37,2 cm
Weight packing	16,85 kg
Type Packaging	Kraft cardboard box
PCB	1
Custom code	