

Features

- Accepts cable diameters of upto 48mm
- Can be used with a maximum panel thickness of upto 2.5mm Thick.
- REACH and ROHS Compliant

RS PRO Black Polychloroprene 60mm Cable Grommet for Maximum of 48mm Cable Dia

RS Stock No.: 0428002



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

This 60 mm round cable grommet from RS PRO is designed for easy installation, providing protection for wires while keeping your project neat. To use, simply cut a hole to the required size, insert the grommet into the panel, and pass the cable through.

It accommodates cables with diameters between 1 mm and 29 mm and can also function as a blanking grommet to seal unused panel openings, preventing dust and moisture ingress. This grommet is compatible with panels up to a maximum thickness of 2mm.

Made from black polychloroprene rubber, it is suitable for temperatures ranging from -30°C to +90°C.

Specifications

Grommet Type	Cable Grommet
Material	Polychloroprene
Colour	Black
Maximum Panel Thickness	2.5mm
Minimum Cable Diameter	1mm
Maximum Cable Diameter	48mm
Panel Hole Diameter	60mm
Minimum Operating Temperature	90°
Maximum Operating Temperature	-30°

Approvals

Standards Met	REACH, RoHS
---------------	-------------