

LONG LIFE CUTTING METAL

PRO

- 1 Robust aluminium oxide grains for long-lasting performance
- 2 Resin matrix for strength and resistance to heat
- 3 Strong fibreglass net reinforces the disc



BOSCH

PRO METAL BONDED CUTTING DISC

PRO


- ▶ For cutting metal in general metalworking applications
- ▶ Highly efficient for metalworkers: Long Life
- ▶ Designed for cutting metal
- ▶ With 22.23 mm bore for standard locking nut angle grinders



PRODUCT PROPERTIES						ORDERING INFORMATION					
Specification	Diameter mm	Bore diameter mm	Thickness mm	X-LOCK	oSa	Packaging type	Pack quantity	Minimum order quantity	Barcode 3 165 140...	Part number	
With depressed centre											
A 30 S BF	180	22.23	3.0	-	●	U0	1	25	149 389	2 608 600 316	
Straight											
A 30 S BF	180	22.23	3.0	-	●	U0	1	25	149 433	2 608 600 321	
With depressed centre											
A 30 S BF	180	22.23	3.0	-	-	U0	1	20	658 584	2 608 603 161	
Straight											
A 30 S BF	180	22.23	3.0	-	-	U0	1	40	658 263	2 608 603 167	
With depressed centre											
A 30 S BF	230	22.23	2.5	-	●	U0	1	25	116 466	2 608 600 225	
A 30 S BF	230	22.23	2.5	-	-	U0	1	25	631 431	2 608 619 776	
A 30 S BF	230	22.23	3.0	-	●	U0	1	25	116 473	2 608 600 226	
Straight											
A 30 S BF	230	22.23	3.0	-	●	U0	1	25	149 495	2 608 600 324	
With depressed centre											
A 30 S BF	230	22.23	3.0	-	-	U0	1	25	658 591	2 608 603 162	
Straight											
A 30 S BF	230	22.23	3.0	-	-	U0	1	25	658 270	2 608 603 168	
A 30 R BF	305	22.23	3.3	-	●	U0	1	10	252 829	2 608 600 649	


BOSCH