

Cable cutter Professional electric with switchable opening spring (43662)



wiha 
Tools that work for you

Wiha Werkzeuge GmbH
Obertalstraße 3-7 78136 Schonach
E-Mail: info.de@wiha.com
Tel.: +49 (0)7722 959-0

Article number: Z50321006

Order no.: 43662

EAN: 4010995436629

Lowers your costs: Durable thanks to high-quality, chrome-plated plier surface to prevent corrosion.

Protects your health: Reduces strain from continuous work thanks to opening spring.

Increases your efficiency: Clean work thanks to cable cutting without crushing.

Offers you full protection: Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.
VDE and GS tested

Manufactured acc. to IEC 60900.

Application:

Cable cutter for cutting of copper and aluminium cables without crushing, also suitable for stripping.

Not for steel cable, wires and copper conductors with hard coatings.

For work in the area of live parts up to 1,000 V AC.

Customs tariff number	82032000
-----------------------	----------

Blister pack issue	No
--------------------	----

Cross-sectional area, max.	60 mm ²
----------------------------	--------------------

Overall length (mm)	210 mm
---------------------	--------

Overall length (inches)	8 1/4"
-------------------------	--------

VDE article	Yes
-------------	-----
