

QUICK CAB PCQ 604021 T



Sample photo

Order symbol: CAB PCQ 604021 T
Product nbr: 8113078
Description: Cabinet, PC
Remarks: Smoked transparent cover

EAN: 6418074011121
El. number:
 Finland: 3421926
 Italy: 7682060
 Sweden: 2540109
 Norway:

Including: Base with screws for mounting plate/DIN-rail, internal corner plugs, cover with PUR gasket and CS 12137 cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		600	400	210	Ingress Protection (EN 60529): IP 66/67
inch:		23.6	15.7	8.3	Impact Resistance (EN 62262): IK 08
Materials:					Electrical insulation: Totally insulated
Material:		Polycarbonate			Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:		RAL 7035			UV resistance: UL 508
Cover colour:		Smoked grey			Flammability Rating (UL 746 C 5): UL 746C 5V
Cover screws material:		Polyamide			Glow Wire Test (IEC 695-2-1) °C: 960
Cover screws colour:		RAL 5023			NEMA Class: NEMA 1, 4, 4X, 12, 13
Gasket material:		Polyurethane			
Temperatures:					Certificates:
Short term:		-40 ... 120 °C			Germanischer Lloyd (GL)
Continuous:		-40 ... 80 °C			Underwriters Laboratories
Short term:		-40 ... 250 °F			Fimko
Continuous:		-40 ... 175 °F			Lloyds Register of Shipping (LR)
Accessories:					Europe EN 62208: 2003
EKIV 64H		Mounting plate			UL Canada
EKIV 37		DIN-35 Mounting rail			Gost R
FP A 64		Swing-out door/Front plate			
MB 12225 AL		Swing door set			
FP 18x3-64		Front plate			
DRF 63/64		DIN rail frame set			
PAT 12040		Hinge set			

