




Connectors > PCB Connectors > PCB Headers & Receptacles > Header Assembly: Wire-to-Board, 15A, gold or tin plated



PCB Connector Type: **PCB Mount Header**

PCB Mount Orientation: **Horizontal**

Connector System: **Wire-to-Board**

Number of Positions: **4**

Number of Rows: **1**

[All Header Assembly: Wire-to-Board, 15A, gold or tin plated \(120\)](#)

Features

Product Type Features

PCB Connector Type	PCB Mount Header
Connector System	Wire-to-Board
Header Type	Fully Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Connector Product Type	Connector Assembly

Configuration Features

PCB Mount Orientation	Horizontal
Number of Positions	4
Number of Rows	1

Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features



Contact Mating Area Plating Material Thickness	.76 μm[30 μin]
Contact Mating Area Plating Material	Gold (Au)
Contact Type	Pin
Contact Current Rating (Max)	8 A

Termination Features

Termination Method to PCB	Through Hole - Solder
---------------------------	-----------------------

Mechanical Attachment

Mating Retention	With
PCB Mount Retention Type	Retention Leg
Mating Alignment Type	Polarization
PCB Mount Retention	With
PCB Mount Alignment	Without
Connector Mounting Type	Board Mount
Mating Alignment	With

Housing Features

Housing Material	Polyester GF
Centerline (Pitch)	3.81 mm [.15 in]

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Box, Tube
------------------	-----------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	



Current ECHA Candidate List: JAN 2025
(247)
Candidate List Declared Against: JAN 2025
(247)
Does not contain REACH SVHC

Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
-----------------	--

Solder Process Capability

Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-178288-4
DYNAMIC 3100 REC HSG 4P

Also in the Series | Dynamic 3000 Series



Connector Contacts(94)



Connector Hardware(8)




Power Contacts(94)



Rectangular Connector Housings(108)



Rectangular Power Connectors(386)



Standard Rectangular Connectors(110)



Wire-to-Board Connector Assemblies & Housings(47)

Customers Also Bought




TE Part #1-480285-0
10P CMNL PLUG HSG M/M NATL



TE Part #2842121-6
6P,2MM,BRK HDR,SRRT,2.8,SN,BOX



TE Part #2294417-1
INDUSTRIAL MINI I/O HDR TYPE I EMBOSS



TE Part #284539-8
8 POS TERMI-BLOK 900 W.S.F. 3, EMBOSS



TE Part #2-917809-3
DYNAMIC D-5 TAB HSG D/R 6P Y-Y



TE Part #1-175218-3
DYNAMIC D-3 REC CONT. L AU 0.76 L /P



TE Part #1-2229803-1
D3950 HDR 11POS 1ROW X KEY



TE Part #3-1462039-7
IM07DGR=IM RELAY 200mW 24V



TE Part #6-1423091-2
T9AS1D14-5



TE Part #170084-2
250 FASTON,REC.,18-14 AWG,TPPB

Documents

Product Drawings

DYNAMIC D3100 HDR ASY 4P H K/X

English

CAD Files

Customer View Model

ENG_CVM_1-178294-3_B1.3d_stp.zip

English

Customer View Model



[ENG_CVM_1-178294-3_B1.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_1-178294-3_B1.3d_igs.zip](#)

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English

Agency Approvals

TUV Certificate

English