


Snap-in markers - UCT-EM (12X6) - 0801503

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Snap-in markers, Sheet, white, unlabeled, can be labeled with: THERMOMARK CARD, BLUEMARK CLED, BLUEMARK LED, TOPMARK LASER, Mounting type: snapped into marker carrier, Lettering field: 12 x 6 mm



Key commercial data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 046356 673501
Weight per Piece (excluding packing)	12.56 g
Custom tariff number	39269097
Country of origin	Germany

Technical data

Dimensions

Length (b)	12 mm
Width (a)	6 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
---------------------------------	-------------------

General

Color	white
Components	free from silicone and halogen
Inflammability class according to UL 94	V0
Material	PC
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	30
Number of individual labels per row	5
RoHS compliant	Yes
Printability	Thermal transfer
	Inkjet printing

Snap-in markers - UCT-EM (12X6) - 0801503

Technical data

General

Device	5146464 THERMOMARK CARD
	0801736 THERMOMARK CARD-UCT-MAG9
	5147888 BLUEMARK LED
	5147999 BLUEMARK CLED
Ink ribbon	0801371 THERMOMARK-RIBBON 110-TC
	5147421 BLUEMARK FLUID-CARTRIDGE
	5146662 BLUEMARK CLED-FLUID-CARTR.
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Wipe resistance test result	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	DIN 50018:2013-05
Climate level	AHT 1.0 S
Cycles	2
Condensation test result	Test passed
Wipe resistance of test specification inscriptions	IEC 61010-1:2010-06
Result	Test passed
Marking mounting type	snapped into marker carrier

Classifications

eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27141137
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137

ETIM

ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

UNSPSC

UNSPSC 6.01	30211811
-------------	----------

Snap-in markers - UCT-EM (12X6) - 0801503

Classifications

UNSPSC

UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Accessories

Accessories

Magazine

Magazine - THERMOMARK CARD-UCT-MAG9 - 0801736



Magazine for the THERMOMARK CARD printer, for accommodating UCT sheets UCT-EM (12 x 3.3) and UCT-EM (12 x 6)

Drawings

Pictogram

