

Wet Area Combination Lock 2810



Product Description

The 2810 wet area combination lock is a 4-wheel combination lock designed for use in chlorinated environments. Available in single-use public mode and private mode*, and featuring up to 10,000 unique combinations, this corrosion resistant combination lock is ideal for use on lockers and personal storage areas in gyms, spas, swimming pools and leisure facilities.

- **Versions:**
 - Public and private mode available
 - Standard fit with countersunk screws
 - Twist resist with pan head screws
- **Movement:**
 - 1 – Right Hand (clockwise to open)
 - 2 – Left Hand (anti-clockwise to open)
- Zinc die-cast construction
- **Combinations:** 4-Wheel combination (10,000 codes)
- **Code finding feature:** 10 Disc barrel with shutter cap
- **Code changing function:** only accessible in the un-locked position
- **Finish:**
 - Xylan finish – corrosion resistant as standard
 - Body and Face – black as standard
- **Diameter:** 56 x 28mm (protrudes from door frame)
- **Nut fixing:** 3/4" – 27 UN x 20mm long (15.9mm A/F)
- **Cam fixing:** 8mm Sq. with M4 thread
- Epoxy logo badge (customer logo available on request)

Options

Product Code	Housing Fixing	Body Width	Body Depth	Finish	Cam Fixing	Lock Feature	Code Combinations	Body Length
2810	Nut Fixing	56	28	Black Xylan	Screw	Standard	10000	20

Technical Drawing

