



Part Number : [1300390376](#)
Product Description : Mini-Change Terminator, Female, 5 Pole
Series Number : 130039
Status : Active
Product Category : Circular Industrial Connectors
Engineering Number : DN150



Documents & Resources

Drawings
[1300390376_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Part Details

General

Status	Active
Category	Circular Industrial Connectors
Series	130039
Description	Mini-Change Terminator, Female, 5 Pole
IP Rating	IP67
Product Name	Mini-Change
Type	Terminator
UPC	78172553529

Electrical

Current - Maximum per Contact	8.0A
Voltage - Maximum	50V AC/DC

Physical

Cable Diameter	N/A
Coupling Type	Internal Thread
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Female
Keyway	Single
Material - Connector Body	PVC
Material - Contact	Copper Alloy
Material - Coupling Nut	Zinc Die-Cast
Material - Plating Mating	Gold
Net Weight	58.121/g
Orientation	Straight
Poles	5
Temperature Range - Operating	0°C to +60°C
Wire Size (AWG)	N/A

This document was generated on Mar 27, 2025