

Angle Impact Wrench LXT®

DTL300

18V, 1/2", C ring / PIN-detent 340 Nm , 0 - 3200 min⁻¹

Model DTL300 is an angle impact wrench powered by 18V LXT Li-Ion battery

This model has a high torque that can loosen even stuck bolts. It has been developed to target work in tight spaces. Features LED job light, Slim tool head, 4 modes: Low, Med, High, Automatic impact stop system in forward/reverse rotation.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Max Fastening Torque Impact Drill	340 Nm
No load speed	0 - 1000 / 1500 / 3200 min ⁻¹
Impacts per Minute (IPM)	0 - 1800 / 2800 / 4000 min ⁻¹
Drive Square	1/2 "
Tightening Capacity Standard Bolt	M10 -M20
Tightening Capacity High Tensile Bolt	M10 -M16
Sound Power Level (L _{WA})	108 dB(A)
Sound Pressure Level (L _{pA})	100 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	1,8 - 2,1 kg
Product Dimensions (L x W x H):	414 x 80 x 92 mm
Brushless Motor	✓

User benefits

- Ideal for working in tight spaces and overhead applications
- Variable speed control dial enables user to match the speed to the application for greater versatility
- Built-in LED light illuminates the work area
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions

Link to product - www.makitauk.com



Related products

Other

User manual

Parts drawing