



|                                 |                                                                                                           |                                                                                                                                                                                              |
|---------------------------------|-----------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Type</b> .....               | 16621 101 121                                                                                             | <b>Features (Technical)</b> .....                                                                                                                                                            |
| <b>Designation</b> .....        | Safety Light                                                                                              | SMD LED                                                                                                                                                                                      |
| <b>Battery required</b> .....   | 2 X CR2032 cells                                                                                          | Push switch (White high/White low/White blink/Red/Red blink/Off)                                                                                                                             |
| <b>LED</b> .....                | 4 pcs Samsung LM281B cool white LED, CCT 4500K-5500K<br>3 pcs SMD 2835 Red LED                            | 4 second Memory Wash feature<br>- No brightness and mode memory function after 4 s<br>- If longer than 4s in any mode light switch directly off<br>- Always start in high mode when light on |
| <b>Luminous intensity</b> ..... | High 25 lm (6.25 cd)<br>Low 10 lm<br>Red 4 lm                                                             | Double snap hook design (snap hook can twist out the battery cover if replacing the battery)                                                                                                 |
| <b>Run Time</b> .....           | High 2.5 h<br>Low 15 h<br>Red 3 h<br>Red Blinking 45 h (on to off)                                        | Magnetic design: "Stick" it to steel surfaces for hands-free use<br>Magnetic clip<br>Multi-Use: Running/Camping/Lightweight portable                                                         |
| <b>Range</b> .....              | 5 m<br>(calculated distance at maximum luminous intensity with an illuminance of 0.25 lux)                | Eye risk group Exempt<br>2m (6.6 feet) impact resistant<br>IP54 Dust resistant & water resistant<br>10,000 Switch cycle life                                                                 |
| <b>Material</b> .....           | PC (Polycarbonate)<br>ABS<br>PVC<br>Silicone<br>(All contact parts made of bronze or nickel plated steel) |                                                                                                                                                                                              |
| <b>Weight</b> .....             | 25.9 g (without battery)<br>31 g (with battery)                                                           |                                                                                                                                                                                              |
| <b>Dimensions</b> .....         |                                                                                                           |                                                                                                                                                                                              |
| <b>A (with button)</b>          | 45.8 mm                                                                                                   |                                                                                                                                                                                              |
| <b>B</b>                        | 49.5 mm                                                                                                   |                                                                                                                                                                                              |
| <b>C</b>                        | 21.7 mm                                                                                                   |                                                                                                                                                                                              |

**No publication or circulation of data to third parties without consent of VARTA Consumer Batteries**