



## Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCKE
Head type	Plunger head
Product compatibility	XCKJ
Associated body	ZCKJ21 ZCKJD39 ZCKJ2H29 ZCKJD35H7 ZCKJ7H7 ZCKJ9H7 ZCKJD35H29 ZCKJ1H7 ZCKJ5H7 ZCKJ11H7 ZCKJ11 ZCKJ21H29 ZCKJD37H7 ZCKJ6 ZCKJ21H7 ZCKJD31H29 ZCKJ6H7 ZCKJ41H29 ZCKJ9 ZCKJ4H29 ZCKJ8H7 ZCKJ11H29 ZCKJD39H7 ZCKJ1 ZCKJD31 ZCKJ6H29 ZCKJ7H29 ZCKJ5H29 ZCKJ41 ZCKJ4 ZCKJ8H29

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

ZCKJ2H7  
 ZCKJ9H29  
 ZCKJ2  
 ZCKJD39H29  
 ZCKJD37H29  
 ZCKJD31H7  
 ZCKJ5  
 ZCKJ7  
 ZCKJ8  
 ZCKJ1H29  
 ZCKJD37  
 ZCKJD35  
 ZCKJ41H7  
 ZCKJ4H7

Movement of operating head	Linear
Type of operator	End plunger spring return metal
Type of approach	Vertical approach, 1 direction

### Complementary

Switch actuation	On end
Positive opening	With
Head material	Metal

### Environment

Ambient air temperature for operation	-40...70 °C
Ambient air temperature for storage	-40...70 °C
Environmental characteristic	Low temperature

### Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	<a href="#">RECh Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

### Contractual warranty

Warranty	18 months
----------	-----------