

HONEYWELL SUPERONE

3205-V1 FFP2 DISPOSABLE MASK

PRODUCT FEATURES

Reference Number

- 1013205-V1

Product Type

- Respiratory Protection

Line

- Molded masks

Range

- Disposable APR



CERTIFICATIONS

EC Category PPE: 3

Quality Assurance: ISO 9001 / 2000,
Module D as per PPER 2016/425/EU

Certifications: EN 149:2001+A1:2009

MAINTENANCE

Life Cycle: 3 years

Storage Information: Temperature range of
storage conditions: -20°C/+40°C

**Maximum relative humidity of storage
conditions:** less than 80 %

MAXIMUM USAGE LEVEL

Can be used in atmospheres containing solid and/or liquid aerosols in concentrations up to 12 (10 in UK, FIN, D, I, S) x WEL*: FFP2 class (average toxicity). "NR" (Non Reusable) marked, it can be used one single shift (according to EN 149:2001+A1:2009). Certain restrictions or limitations may apply in the case of specific contaminants.

LIMITATIONS TO USE

This single-use filtering half-mask should NOT be used in the following situations :

- oxygen concentration is less than 17% (oxygen-deficient atmospheres)
- contaminants or their concentrations are unknown or are immediately dangerous to life or health
- contaminants concentrations exceed levels fixed by applicable health and safety standards or 12 (10 in UK, FIN, D, I, S) x WEL*
- in the presence of toxic or radio-active contaminants
- in the presence of gases or vapors
- in explosive atmospheres
- fire fighting.

TECHNICAL DESCRIPTION

- **STANDARD:** EN149.2001. A1:2009
- **MASK TYPE:** Molded Cup
- **Protection Class:** FFP2
- **Valve:** No
- **Mask Size:** Medium
- ✓ Latex free
- ✓ PVC Free
- ✓ Silicone Free

For More Information

www.honeywellsafety.com/europe

* WEL : Workplace Exposure Limit.