
Features

- Grade 10 sling hook with ball-bearing swivel
- Available from 6mm to 16mm lifting chains
- Available from 1.4t to 10T Working Load Limit
- Allows rotation under both loaded and unloaded conditions
- Sturdy Latch for secure load retention

RS PRO Sling Hook, With Swivel



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO Sling Hook, with Swivel

The RS PRO Sling Hook SHS-B with Ball-Bearing Swivel is a Grade 10 lifting chain component designed for quick and secure attachment to suitable lifting points. The hook is easy to use and features a sturdy latch to help retain the load connection during lifting operations.

The hook eye is fitted with a **ball-bearing swivel**, allowing rotation under both loaded and unloaded conditions. This helps reduce twisting in the chain sling assembly and provides greater flexibility when positioning or handling loads.
Available for **6mm to 16mm chain sizes**, with working load limits from **1.4t to 10t**, this hook is suitable for a range of lifting applications where controlled rotation is required. It is manufactured from high-strength **Grade 10 alloy steel** and finished in luminous red paint for durability and easy identification.

Each component is type tested and fatigue rated to **20,000 cycles at 1.5 times the WLL**, with full traceability through batch marking. It meets **EN 1677-2 +25% WLL** and **AS 3776**, with a safety factor of **4:1**.

The component may also be used with Grade 8 chain to **EN 818-2**, provided the complete chain sling is rated as Grade 8 in accordance with **EN 818-4**.

General Specifications

Product Type	Lifting Hooks
Sub Type	Sling hook with Swivel
Material	Grade 10 Alloy steel
Working Load Limit	See details below
Weight	See details below
Standards/Approvals	EN1677

Stock No.	Product Name	Working Load Limit	Weight (kg)
904886	Sling hook with Swivel	1.4	0.65
904887	Sling hook with Swivel	2.5	0.95
904883	Sling hook with Swivel	4	1.7
904884	Sling hook with Swivel	6.7	3.1
904885	Sling hook with Swivel	10	5.4

Approvals

Declarations	REACH DoC and 2.2 Certificate
Standards Met	EN1677

Similar Products

Stock No.	Brand	Product Name	Product Type	Working Load Limit	Weight (kg)
904899	RS PRO	Lifting Hook	Container	16t	4
904900	RS PRO	Lifting Hook	Container	16t	4
904901	RS PRO	Lifting Hook	Container	16t	4
904897	RS PRO	Lifting Hook	Connecting Link	1.4t	0.08
904898	RS PRO	Lifting Hook	Connecting Link	2.5t	0.18
904888	RS PRO	Lifting Hook	Connecting Link	4t	0.34
904890	RS PRO	Lifting Hook	Connecting Link	6.7t	0.68
904891	RS PRO	Lifting Hook	Connecting Link	10t	1.22
904892	RS PRO	Lifting Hook	Connecting Link	16t	2.13
904893	RS PRO	Lifting Hook	Connecting Link	19t	3
904894	RS PRO	Lifting Hook	Connecting Link	26.5	5.22
904896	RS PRO	Lifting Hook	Connecting Link	40	9.55
904910	RS PRO	Lifting Hook	Self-Lock w/ Eye	1.4	0.5
904911	RS PRO	Lifting Hook	Self-Lock w/ Eye	2.5	0.9
904903	RS PRO	Lifting Hook	Self-Lock w/ Eye	4	1.5
904904	RS PRO	Lifting Hook	Self-Lock w/ Eye	6.7	2.7
904905	RS PRO	Lifting Hook	Self-Lock w/ Eye	10	5.7
904906	RS PRO	Lifting Hook	Self-Lock w/ Eye	16	7.9
904907	RS PRO	Lifting Hook	Self-Lock w/ Eye	19	11.2
904908	RS PRO	Lifting Hook	Self-Lock w/ Eye	26.5	20.5
904909	RS PRO	Lifting Hook	Self-Lock w/ Eye	40	40.4
904879	RS PRO	Lifting Hook	Sling Hook	1t	0.7
Stock No.	**Brand**	**Product Name**	**Product Type**	**Working Load Limit**	**Weight (kg)**
904880	RS PRO	Lifting Hook	Sling Hook	2t	1.3

904881	RS PRO	Lifting Hook	Sling Hook	3t	2.3
904882	RS PRO	Lifting Hook	Sling Hook	5t	4.6
904886	RS PRO	Lifting Hook	Sling Hook with Swivel	1.4	0.65
904887	RS PRO	Lifting Hook	Sling Hook with Swivel	2.5	0.95
904883	RS PRO	Lifting Hook	Sling Hook with Swivel	4	1.7
904884	RS PRO	Lifting Hook	Sling Hook with Swivel	6.7	3.1
904885	RS PRO	Lifting Hook	Sling Hook with Swivel	10	5.4
904877	RS PRO	Lifting Hook	Sling Hook with Eye	1.4t	0.27
904878	RS PRO	Lifting Hook	Sling Hook with Eye	2.5t	0.65
904912	RS PRO	Lifting Hook	Sling Hook with Eye	4t	1.22
904913	RS PRO	Lifting Hook	Sling Hook with Eye	6.7t	2.43
904871	RS PRO	Lifting Hook	Sling Hook with Eye	10t	3.81
904872	RS PRO	Lifting Hook	Sling Hook with Eye	16t	6.2
904874	RS PRO	Lifting Hook	Sling Hook with Eye	19t	11.5
904875	RS PRO	Lifting Hook	Sling Hook with Eye	26.5t	12.2
904876	RS PRO	Lifting Hook	Sling Hook with Eye	40t	17.5