

Datasheet

Item No. 92.030.1053.0

Distributor GST18I3V 2P1T V WS

T-connector GST18i3, 3 pole, 1 input, 2 outputs, 250V/16A, color of coding: white



Item No.	92.030.1053.0
EAN	4015573369382
order unit	100 Piece(s)

Approvals



Technical data

General

Rated current	16 A
Rated voltage	250 V
Rated impulse voltage	4 kV
Pollution degree	2
Mechanical coding	Yes
Interlockable	Yes
Color of coding/ contact carrier	White

Model

Number of poles	3
Number of inputs	1
Number of outputs	2
Type of fastening	No
Degree of protection (IP)	IP40
Type of distributor	T-distributor

Material

Housing material	Polyamide
Halogen free	Yes
Contact material	CuZn
Insulation components continuous temperature	100 °C
Surface finish	Silver-plated

Dimensions

Length	44 mm
Width	28.2 mm
Height	43 mm

Drawings

Teile-Nr./part number	Farbe/colour	Typ/type
92.030.1053.0	weiß/white	GST1813V 2P1T V ws
92.030.1053.1	schwarz/black	GST1813V 2P1T V sw

Freioleranz nach DIN	CD - Zeichnung, keine manuellen Änderungen	I. Verwendung: -	Bl.: 1 von 1
Maßstab: 2:1	Entworfen: 07.12. 2001, Bauer F. 104	Geprüft: [Signature]	Zeichnung Nr.: 92.030.1053.0 01K
		Benennung: VERTEILER_T_FORM distribution rack T-form	
Änderung:			