

Product datasheet

Specifications



module Profibus DP slave - SUBD-9 connector

VW3E704000000

EAN Code: 3606485306940

Main

Range of product	Modicon LMC078
Product or component type	Profibus DP communication module
Range compatibility	Modicon LMC078
Product compatibility	Motion controller

Complementary

Physical interface	RS485
Method of access	Master/slave
Integrated connection type	Profibus DP - 1 female SUB-D 9 connector, transmission rate: 12 Mbit/s

Environment

Standards	UL 508 IEC 61131-2 zone B CSA C22.2 No 142
Product certifications	cULus CSA CE
Marking	CE
Ambient air temperature for operation	5...55 °C
Ambient air temperature for storage	-25...70 °C
Relative humidity	5...95 % without condensation
IP degree of protection	IP20 conforming to IEC 61131-2
Pollution degree	2
Operating altitude	0...2000 m
Vibration resistance	10 m/s ² on direct mounting
Shock resistance	100 m/s ²

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.700 cm
Package 1 Width	8.300 cm
Package 1 Length	11.200 cm
Package 1 Weight	104.000 g

Unit Type of Package 2	S01
Number of Units in Package 2	12
Package 2 Height	15.000 cm
Package 2 Width	15.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	1.436 kg

Contractual warranty

Warranty (in months)	18
-----------------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better



Materials and Substances

Packaging made with recycled cardboard

No

Packaging without single use plastic

No

Use Longer



Lifetime extension

Repair

No

Use Again



Repack and remanufacture

Take-back

No