

Han CGM-M M40x1,5 D.20-26mm



Image is for illustration purposes only. Please refer to product description.

Part number	19 00 000 5097
Specification	Han CGM-M M40x1,5 D.20-26mm
HARTING eCatalogue	https://harting.com/19000005097

Identification

Category	Accessories
Series of hoods/housings	Han® CGM-M
Type of accessory	Cable gland

Technical characteristics

Tightening torque	≤15 Nm (depending on the cable and the seal insert used)
Wrench size	50
Limiting temperature	-40 ... +100 °C
Degree of protection acc. to IEC 60529	IP68 IP69 / IPX9K acc. to ISO 20653
Size	M40
Clamping range	20 ... 26 mm
Width across corners	55 mm

Material properties

Material (cable glands)	Brass
Material (seal)	NBR
Material (clamping ring)	Polyamide (PA)
Surface (accessories)	Nickel plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50



Pushing Performance
Since 1945

Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol Lead
ECHA SCIP number	6d86e660-27db-4390-811a-374604e3d289
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Specifications and approvals

UL / CSA	UL 514B QCRV.E479780 CSA-C22.2 No. 18.3 QCRV7.E479780
Approvals	DNV GL

Commercial data

Packaging size	1
Net weight	180.9 g
Country of origin	Germany
European customs tariff number	74122000
GTIN	5713140123830
eCl@ss	27140801 Screwed cable gland (electrical)
ETIM	EC000441
UNSPSC 24.0	39121431