



TE Internal #: 6-1813099-1

TE Internal Description: 2.5mm SOCKET HSG ASSEMBLY(GREY 4 POS)

CIRCULAR DIN HOUSINGS

[View on TE.com >](#)



All CIRCULAR DIN HOUSINGS (51)

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUL 2021 (219) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts



TE Part # CAT-C4962-B128
CIRCULAR DIN BACKSHELLS



TE Part # 828920-1
EINZELADERDICHTUNG



TE Part # 828922-1
2,5MM CAVITY PLUG FOR 5,4MM DI



TE Part # CAT-R7602-T273
ROUND CONNECTOR SYSTEM, PIN AND SOCKET



TE Part # 185636-1
PROTECT CAP 2.5MM PLUG



TE Part # 185793-1
90 DEG CAP CORRUGTD TUBE

Customers Also Bought



TE Part #DT04-6P-CE02
REC, 6P, BLK, E



TE Part #1060-14-0122
PIN, SF, SIZE 16, 14-18, NI/SN



TE Part #403289-000
CWT-3

Documents

Product Drawings
2.5mm SOCKET HSG ASSEMBLY(GREY 4 POS)
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_6-1813099-1_A_c-6-1813099-1-a.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_6-1813099-1_A_c-6-1813099-1-a.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_6-1813099-1_A_c-6-1813099-1-a.3d_stp.zip

6-1813099-1

2.5mm SOCKET HSG ASSEMBLY(GREY 4 POS)



English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.