




PRODUCT-DETAILS

OT2000E03K

OT2000E03K SWITCH-DISCONNECTOR



概要信息	
产品型号	OT2000E03K
产品ID	1SCA108359R1001
欧洲商品编号(EAN)	6417019427034
目录说明	OT2000E03K SWITCH-DISCONNECTOR
详细描述	3-pole, front operated, base mounted switch-d disconnecter with black direct mount handle, terminal bolt kit included

ABB EcoSolutions	
产品寿命终止后的拆解指南	1SCC301121M0201
环境信息	1SCC301268D0201
产品环境声明 - EPD	1SCC301304D0201

Material Compliance	
Conflict Minerals Reporting Template	9AKK108467A5658

(CMRT)	
REACH Declaration	1SCC011021D0201
RoHS信息	1SCC011020D0201
RoHS状态	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
Toxic Substances Control Act - TSCA	1SCC011025D0201

Popular Downloads

数据手册, 技术资料	1SCC301020C0201
说明书和手册	1SCC301078M0205
机械制图	1SCC301735F0002 1SCC301734F0002
产品环境声明 - EPD	1SCC301304D0201
产品寿命终止后的拆解指南	1SCC301121M0201

环境条件

防护等级	Front IP00
环境信息	1SCC301268D0201
污染等级	3

订货信息

最小起订量	1 piece
海关关税号	85365080
原产地	Finland (FI)

尺寸

产品净宽	472.5 mm
产品净高	376.5 mm
产品净深	167 mm
产品净重	22.8 kg

包装信息

1级包装单元	box 1 piece
1级包装宽度	394 mm
1级包装长度	534 mm
1级包装高度	368 mm
1级包装 总重	46.9 kg
1级包装 EAN	6417019427034

技术参数

额定发热电流（自由空气）(I _{th})	Θ = 40 °C 2000 A
防护等级	Front IP00
两相之间距离	Standard
Handle Color	Black

手柄类型	Direct mounted pistol type handle
Lock Type	Yes
机械寿命	6000
安装类型	Base mounting
极数	3P
操作模式	Front operated
污染等级	3
导线端子位置	Top In - Bottom Out Bottom In - Top Out
功率损耗	at Rated Operating Conditions per Pole 55 W
额定限制短路电流 (I_{nc})	(1250 A fuse, 415 V) 80 kA (1250 A fuse, 500 V) 100 kA
额定冲击耐受电压 (U_{imp})	12 kV
额定绝缘电压 (U_i)	acc. to IEC/EN 60664-1 1000 V
额定工作电流 AC-21B (I_e)	(380 ... 415 V) 2000 A (500 V) 2000 A (690 V) 2000 A
额定工作电流 AC-22B (I_e)	(380 ... 415 V) 2000 A (500 V) 2000 A (690 V) 2000 A
额定工作电压	Main Circuit 1000 V
额定短路接通容量 (I_{cm})	(690 V) 176 kA
额定不间断电流 (I_{cw})	for 1 s 55 kA
特殊功能	No
标准	IEC 60947-3
开关操作机构	Mechanism at the End of the Switch 03 (Left Side)
端子类型	Lug terminals
拧紧力矩	acc. IEC 60947-1 50 ... 75 N·m

UL/CSA适用的技术参数

拧紧力矩	acc. IEC 60947-1 50 ... 75 N·m
------	--------------------------------

认证及声明（文件编码）

A2L Certificate – IEC	1SCC301338D0201
ATEX认证	No certification needed
符合性声明 - CE	1SCC301176D2702
DNV GL Certificate	1SCC301184D0203
UL认证	No certification needed
VDE认证	No certification needed

分类

对象分类代码	Q
ETIM 8	EC000216 - Switch disconnecter
ETIM 9	EC000216 - Switch disconnecter (low voltage)
e级	V11.1 : 27371403
WEEE 类别	5. Small Equipment (No External Dimension More Than 50 cm)
E-Number (Finland)	3660820

分类

低压产品及系统 → 开关类产品 → 隔离开关

