

DATA SHEET

PANISDNxxN

19" ISDN telephone panel with 50 or 60 ports - 1U



DESCRIPTION / APPLICATION

- ISDN telephone panel 1U equipped with 50 or 60 RJ45 Category 3 ports
- Black Epoxy paint
- Usable in all 19» wall mounted and floor standing cabinets
- 4/5 and 3/6 pairs prewired
- Horizontal printed circuits: DUAL IDC connectors solid or stranded AWG 23 AWG 26
- Grounding by pin
- Connection with metallic insertion tool (reference : MMCMTAT)

PROPERTIES —

NUMBER OF TERMINATION	MATERIAL		
>200	IDC	Housing	
	Phosphor bronze alloy	High impact flame retardant UL94V0	

RELATED PRODUCT —

PART NUMBER	DESIGNATION
MMCMTAT	Punch down tool

ORDERING INFORMATION -

PART NUMBER	DESIGNATION	PACKAGING
PANISDN50N	19" ISDN telephone panel 50 ports – 1U	Unit
PANISDN60N	19" ISDN telephone panel 60 ports – 1U	Unit

