

## Connectors / Weatherproof Connectors

### Watertight Cable Joint IP67 3 pole



#### Technical Specification

<b>Product Code</b>	H65Z-C
<b>Feature 1</b>	Can be temporarily submersed in water
<b>Feature 2</b>	For repairing or extending outdoor cables up to 3 core 2.5mm <sup>2</sup>
<b>Feature 3</b>	Max current 15A
<b>Feature 4</b>	Cable diameter Max 12.5mm Min 6mm
<b>Barcode</b>	5012739065309
<b>CE</b>	Y
<b>Colour</b>	Black
<b>Company DUNS Number</b>	216156018
<b>Country of Origin</b>	China
<b>Current (I)</b>	15

Tel No: 01279 772 772

Email: [sales@greenbrook.co.uk](mailto:sales@greenbrook.co.uk)

Website: [www.greenbrook.co.uk](http://www.greenbrook.co.uk)

<b>Finish body</b>	Gloss
<b>Frequency (Hz) max</b>	60
<b>Frequency (Hz) min</b>	50
<b>Greenbrook Guarantee (Years)</b>	1
<b>HS Code</b>	8536901000
<b>Ingress Protection (IP)</b>	IP67
<b>Installation method</b>	Inline
<b>Knock-out Dimensions</b>	Cable Dia: Max 12.5mm/Min 6mm
<b>Knock-out Qty</b>	2
<b>Materials Main Body</b>	Nylon
<b>Min Order Qty</b>	1
<b>Operating Temperature Range max C</b>	50
<b>Operating Temperature Range min C</b>	-20
<b>Package Product Max. Length (mm)</b>	240
<b>Package Product Max. Height (mm)</b>	35
<b>Package Product Max. Width (mm)</b>	75
<b>Product (only) Max. Depth (mm)</b>	120
<b>Product (only) Max. Height (mm)</b>	32
<b>Product (only) Max. Width (mm)</b>	32
<b>Product Weight net (g)</b>	68.5
<b>Sales Pack Qty</b>	1
<b>StatusCode</b>	Active
<b>UKCA</b>	Y
<b>Voltage (VAC) MAX (V)</b>	240
<b>Voltage (VAC) Min (V)</b>	220
<b>Voltage (VAC) Rated (V)</b>	230
<b>Feature 5</b>	32 x 120mm

Tel No: 01279 772 772

Email: [sales@greenbrook.co.uk](mailto:sales@greenbrook.co.uk)Website: [www.greenbrook.co.uk](http://www.greenbrook.co.uk)