

## Features

- Carbon Steel
- Zinc Plated
- M20
- Securing, lifting and loading
- DIN 582

## RS PRO M20 Eye Nut

RS Stock No.: 124-4844



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

## Product Description

*A Zinc Plated Eye Nut intended for linear pulling loads in the direction of the thread. The Zinc Plated Eye Bolt is proof tested and supplied complete with test certificate.*

*Suitable for a variety of applications including tensioning wires, securing loads and lifting.*

*Not intended for use where the load is perpendicular to the thread. In these instances the bolt could unscrew and move, or twist and break.*

## General Specifications

Type	Eye Nut
Working Load Limit	1.2 ton
Material	Carbon Steel
Finish	Zinc Plated

## Mechanical Specifications

Eye Diameter	40mm
Thread Type	UNC
Thread Size	M20
Thread Length	16mm
Thread Diameter	20mm
Collar Diameter	40 mm
Collar Thickness	16 mm
Outside Diameter	72mm
Overall Height	71 mm
Weight each	352g

## Approvals

Compliance/Certifications	DIN 582
---------------------------	---------